

●もっとも広い用途で使用されている汎用ドリルです。

This drill is applied for general purpose.




直径 2.0mm 未満の表面は白（無着色）です。
Less than 2.0mm in the diameter is the bright finishes.



Dc > 13.0
S形



Dc ≤ 13.0
円すい



LIST 500

オーダ方法 SD 直径

単位 (Unit) : mm

直径 Dc	溝長 ℓ	全長 L	在庫 Stock	参考価格(円) Price (¥)
0.2	3	19		1,010
0.21				1,310
0.22				1,310
0.23				1,310
0.24				1,310
0.25	3.5	20		1,230
0.26				1,310
0.27				1,310
0.28				1,310
0.29				1,310
0.3				634
0.31				790
0.32				790
0.33				790
0.34				790
0.35	5.5	24		740
0.36				790
0.37				790
0.38				790
0.39				790
0.4				524
0.41				654
0.42				654
0.43				654
0.44				654
0.45	7.5	27		616
0.46				654
0.47				654
0.48				654
0.49				654
0.5			●	423
0.51				547
0.52				547
0.53				547
0.54				547
0.55	8.5	30		515
0.56				547
0.57				547
0.58				547
0.59				547
0.6				428
0.61				534
0.62				534
0.63				534
0.64				534
0.65	10	32		498
0.66				534
0.67				534
0.68				534
0.69				534
0.7				394
0.71				492
0.72				492
0.73				492
0.74				492
0.75	11	34		463
0.76				492
0.77				492
0.78				492
0.79				492

直径 Dc	溝長 ℓ	全長 L	在庫 Stock	参考価格(円) Price (¥)
0.8	11	34		334
0.81				447
0.82				447
0.83				447
0.84				447
0.85	13	36		421
0.86				447
0.87				447
0.88				447
0.89				447
0.9				359
0.91				447
0.92				447
0.93				447
0.94				447
0.95	18	40		421
0.96				447
0.97				447
0.98				447
0.99				447
1.0				303
1.01				402
1.02				402
1.03				402
1.04				402
1.05				370
1.06				402
1.07				402
1.08				402
1.09			●	402
1.1				356
1.11	20	42		402
1.12				402
1.13				402
1.14				402
1.15				370
1.16				402
1.17				402
1.18				402
1.19				402
1.2				334
1.21				402
1.22				402
1.23				402
1.24				402
1.25	22	45		370
1.26				402
1.27				402
1.28				402
1.29				402
1.3				356
1.31				402
1.32				402
1.33				402
1.34				402
1.35	23	48		370
1.36				402
1.37				402
1.38				402
1.39				402

直径 Dc	溝長 ℓ	全長 L	在庫 Stock	参考価格(円) Price (¥)
1.4				356
1.41				402
1.42				402
1.43				402
1.44				402
1.45	23	48		370
1.46				402
1.47				402
1.48				402
1.49				402
1.5				302
1.51				397
1.52				397
1.53				397
1.54				397
1.55				363
1.56				397
1.57				397
1.58				397
1.59				397
1.6				328
1.61	25	50		397
1.62				397
1.63				397
1.64				397
1.65				363
1.66				397
1.67				397
1.68				397
1.69			●	397
1.7				356
1.71				397
1.72				397
1.73				397
1.74				397
1.75				363
1.76				397
1.77				397
1.78				397
1.79				397
1.8				340
1.81	28	52		397
1.82				397
1.83				397
1.84				397
1.85				363
1.86				397
1.87				397
1.88				397
1.89				397
1.9				340
1.91				397
1.92				397
1.93				397
1.94				397
1.95	29	55		363
1.96				397
1.97				397
1.98				397
1.99				397

包装数量：8.0mm 以下 10 本入り、8.0mm を超え 13.0mm 以下 5 本入り、13.0mm を超え 2 本入り。

参考価格は 1 本あたりの価格です。

Number of drill bits per package: 10 per package if below 8.0 mm, 5 per package if between 8.0 and 13.0 mm, 2 per package if over 13.0 mm. Price is for one drill bit.

直径許容差：h8 (0.01mm サイズは 0 ~ 0.008mm。ただし、0.05mm サイズは h8) 直径 1mm 未満は 0 ~ 0.01mm 1 本入りの鉄工用ドリル SDP (G-6) もご利用ください。ただし、SDP の直径 4mm 以下は 2 本入りです。