


CoroDrill® 462-XM 小径ソリッドドリル

汎用

TCHA JS7
SIG 130°

							P M K N S O					寸法, mm, inch									
DC	DC*	LU	LU*	ULDR	CZC _{MS}	型番	H10F	H10F	H10F	H10F	H10F	DCON _{MS}	DCON _{MS} *	OAL	OAL*	LF	LF*	LCF	LCF*	PL	PL*
0.03	.001	0.3	.010	8	3	462.1-0030-002A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.496	0	.014	0.0	.000
0.04	.002	0.3	.012	7	3	462.1-0040-003A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.496	0	.016	0.0	.000
0.05	.002	0.4	.014	7	3	462.1-0050-003A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.496	0	.018	0.0	.000
0.06	.002	0.4	.016	6	3	462.1-0060-004A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.496	0	.020	0.0	.001
0.07	.003	0.5	.018	6	3	462.1-0070-004A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.495	0	.024	0.0	.001
0.08	.003	0.5	.020	6	3	462.1-0080-005A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.495	0	.028	0.0	.001
0.09	.004	0.5	.020	5	3	462.1-0090-005A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.495	0	.028	0.0	.001
0.10	.004	0.5	.020	5	3	462.1-0100-005A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.495	0	.028	0.0	.001
0.11	.004	0.5	.020	4	3	462.1-0110-005A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.495	0	.028	0.0	.001
0.12	.005	0.5	.020	4	3	462.1-0120-005A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.495	0	.028	0.0	.001
0.13	.005	0.8	.031	6	3	462.1-0130-008A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.495	1	.039	0.0	.001
0.14	.006	0.8	.031	5	3	462.1-0140-008A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.495	1	.039	0.0	.001
0.15	.006	0.8	.031	5	3	462.1-0150-008A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.495	1	.039	0.0	.001
0.16	.006	1.1	.043	6	3	462.1-0160-011A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.494	1	.055	0.0	.001
0.17	.007	1.1	.043	6	3	462.1-0170-011A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.494	1	.055	0.0	.002
0.18	.007	1.1	.043	6	3	462.1-0180-011A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.494	1	.055	0.0	.002
0.19	.007	1.1	.043	5	3	462.1-0190-011A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.494	1	.055	0.0	.002
0.20	.008	1.5	.059	7	3	462.1-0200-015A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.494	1	.071	0.0	.002
0.21	.008	1.5	.059	7	3	462.1-0210-015A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.494	1	.071	0.0	.002
0.22	.009	1.5	.059	6	3	462.1-0220-015A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.494	1	.071	0.1	.002
0.23	.009	1.5	.059	6	3	462.1-0230-015A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	38.0	1.494	1	.071	0.1	.002
0.24	.009	1.5	.059	6	3	462.1-0240-015A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.494	1	.071	0.1	.002
0.25	.010	1.9	.075	7	3	462.1-0250-019A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.494	2	.087	0.1	.002
0.26	.010	1.9	.075	7	3	462.1-0260-019A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.494	2	.087	0.1	.002
0.27	.011	1.9	.075	7	3	462.1-0270-019A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.494	2	.087	0.1	.002
0.28	.011	1.9	.075	6	3	462.1-0280-019A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.493	2	.087	0.1	.003
0.29	.011	1.9	.075	6	3	462.1-0290-019A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.493	2	.087	0.1	.003
0.30	.012	1.8	.071	6	3	462.1-0300-018A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.493	2	.094	0.1	.003
0.31	.012	1.8	.071	5	3	462.1-0310-018A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.493	2	.094	0.1	.003
0.32	.013	1.8	.071	5	3	462.1-0320-018A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.493	2	.094	0.1	.003
0.33	.013	1.8	.071	5	3	462.1-0330-018A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.493	2	.094	0.1	.003
0.34	.013	1.8	.071	5	3	462.1-0340-018A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.493	2	.094	0.1	.003
0.35	.014	2.2	.087	6	3	462.1-0350-022A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.493	2	.110	0.1	.003
0.36	.014	2.2	.087	6	3	462.1-0360-022A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.493	2	.110	0.1	.003
0.37	.015	2.2	.087	5	3	462.1-0370-022A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.493	2	.110	0.1	.003
0.38	.015	2.2	.087	5	3	462.1-0380-022A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.493	2	.110	0.1	.003
0.39	.015	2.7	.106	6	3	462.1-0390-027A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.493	3	.142	0.1	.004
0.40	.016	2.7	.106	6	3	462.1-0400-027A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.493	3	.142	0.1	.004
0.41	.016	2.7	.106	6	3	462.1-0410-027A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.492	3	.142	0.1	.004
0.42	.017	2.7	.106	6	3	462.1-0420-027A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.492	3	.142	0.1	.004
0.43	.017	2.7	.106	6	3	462.1-0430-027A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.492	3	.142	0.1	.004
0.44	.017	2.7	.106	6	3	462.1-0440-027A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.492	3	.142	0.1	.004
0.45	.018	2.7	.106	6	3	462.1-0450-027A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.492	3	.142	0.1	.004
0.46	.018	2.7	.106	5	3	462.1-0460-027A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.492	3	.142	0.1	.004
0.47	.019	2.7	.106	5	3	462.1-0470-027A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.492	3	.142	0.1	.004
0.48	.019	2.7	.106	5	3	462.1-0480-027A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.492	3	.142	0.1	.004
0.49	.019	3.2	.126	6	3	462.1-0490-032A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.492	4	.157	0.1	.004
0.50	.020	3.2	.126	6	3	462.1-0500-032A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.491	4	.157	0.1	.005
0.51	.020	3.2	.126	6	3	462.1-0510-032A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.491	4	.157	0.1	.005
0.52	.020	3.2	.126	6	3	462.1-0520-032A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.491	4	.157	0.1	.005
0.53	.021	3.2	.126	6	3	462.1-0530-032A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.491	4	.157	0.1	.005
0.54	.021	3.6	.142	6	3	462.1-0540-036A0-XM	☆	☆	☆	☆	☆	3.0	.118	38	1.496	37.9	1.491	4	.177	0.1	.005

