



ラジアスエンドミル CoroMill® 316 一般フライス加工

センターカット



切れ刃外径公差 (mm)

カッター径	h9
6 < DC ≤ 10	0 ~ -0.036
10 < DC ≤ 18	0 ~ -0.043
18 < DC ≤ 30	0 ~ -0.052

R公差: ±0.01mm

P M K S

DC mm	型番	GC	1730	図	カップ リング サイズ	刃数	寸法, mm	最大切込み APMX	
						ZEFP	DCON LF DN RE		
10	316-10SM210-10005P	●	2		E10	2	9.7 11.8 9.7 0.5	8.0	0.01
	316-10SM210-10008P	●	2			2	9.7 11.8 9.7 0.8	8.0	0.01
	316-10SM210-10010P	●	2			2	9.7 11.8 9.7 1.0	8.0	0.01
	316-10SM350-10005P	●	1			3	9.7 12.4 9.7 0.5	5.5	0.02
	316-10SM350-10010P	●	1			3	9.7 12.4 9.7 1.0	5.5	0.02
	316-10SM450-10005P	●	1			4	9.7 12.4 9.7 0.5	5.5	0.02
	316-10SM450-10010P	●	1			4	9.7 12.4 9.7 1.0	5.5	0.02
	316-10SM450-10015P	●	1			4	9.7 12.4 9.7 1.5	5.5	0.02
	316-10SM450-10020P	●	1			4	9.7 12.4 9.7 2.0	5.5	0.02
	316-10SM450-10030P	●	1			4	9.7 12.4 9.7 3.0	5.5	0.02
	316-12SM210-12005P	●	2		E12	2	11.7 14.0 11.7 0.5	10.0	0.02
	316-12SM210-12008P	●	2			2	11.7 14.0 11.7 0.8	10.0	0.02
12	316-12SM350-12005P	●	1			3	11.7 14.5 11.7 0.5	6.5	0.04
	316-12SM350-12010P	●	1			3	11.7 14.5 11.7 1.0	6.5	0.04
	316-12SM450-12005P	●	1			4	11.7 14.5 11.7 0.5	6.5	0.04
	316-12SM450-12010P	●	1			4	11.7 14.5 11.7 1.0	6.5	0.04
	316-12SM450-12015P	●	1			4	11.7 14.5 11.7 1.5	6.5	0.04
	316-12SM450-12020P	●	1			4	11.7 14.5 11.7 2.0	6.5	0.04
	316-12SM450-12030P	●	1			4	11.7 14.5 11.7 3.0	6.5	0.04
	316-12SM450-12040P	●	1			4	11.7 14.5 11.7 4.0	6.5	0.04
	316-16SM210-16005P	●	2		E16	2	15.5 18.1 15.5 0.5	13.0	0.05
	316-16SM210-16008P	●	2			2	15.5 18.1 15.5 0.8	13.0	0.05
	316-16SM210-16010P	●	2			2	15.5 18.1 15.5 1.0	13.0	0.05
	316-16SM350-16005P	●	1			3	15.5 18.7 15.5 0.5	8.5	0.07
16	316-16SM350-16010P	●	1			3	15.5 18.7 15.5 1.0	8.5	0.07
	316-16SM450-16005P	●	1			4	15.5 18.7 15.5 0.5	8.5	0.07
	316-16SM450-16010P	●	1			4	15.5 18.7 15.5 1.0	8.5	0.07
	316-16SM450-16015P	●	1			4	15.5 18.7 15.5 1.5	8.5	0.07
	316-16SM450-16020P	●	1			4	15.5 18.7 15.5 2.0	8.5	0.07
	316-16SM450-16030P	●	1			4	15.5 18.7 15.5 3.0	8.5	0.07
	316-16SM450-16040P	●	1			4	15.5 18.7 15.5 4.0	8.5	0.07
	316-20SM350-20005P	●	1		E20	3	19.3 21.3 19.3 0.5	11.0	0.13
	316-20SM350-20010P	●	1			3	19.3 21.3 19.3 1.0	11.0	0.13
	316-20SM450-20005P	●	1			4	19.3 21.3 19.3 0.5	11.0	0.13
	316-20SM450-20010P	●	1			4	19.3 21.3 19.3 1.0	11.0	0.13
	316-20SM450-20015P	●	1			4	19.3 21.3 19.3 1.5	11.0	0.13
	316-20SM450-20020P	●	1			4	19.3 21.3 19.3 2.0	11.0	0.13
20	316-20SM450-20030P	●	1			4	19.3 21.3 19.3 3.0	11.0	0.13
	316-20SM450-20040P	●	1			4	19.3 21.3 19.3 4.0	11.0	0.13
	316-25SM550-25010P	●	1		E25	5	24.2 25.6 24.2 1.0	13.5	0.21
	316-25SM550-25015P	●	1			5	24.2 25.6 24.2 1.5	13.5	0.21
25	316-25SM550-25020P	●	1			5	24.2 25.6 24.2 2.0	13.5	0.21

※ 1ケース1個入りです

●=標準在庫

=2020年新製品