


●生材から焼入材まで幅広く対応できます。仕上加工に適しています。

This end mill is suitable for workpiece materials from unhardened steel to hardened material, and for finish milling.



LIST 9382

オーダ方法 商品記号

商品記号 Code	外径 Dc	刃長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 (円) Price (¥)
2GS0.2	0.2	0.4	40	4		5,350
2GS0.3	0.3	0.6				4,670
2GS0.4	0.4	0.8				4,670
2GS0.5 × 4	0.5	1.25				2,590
2GS0.6	0.6	1.25				3,950
2GS0.7	0.7	1.5				3,870
2GS0.8	0.8	2				2,470
2GS0.9	0.9	2				3,400
2GS1 × 4	1	2.5				2,320
2GS1.1	1.1	2.5				4,350
2GS1.2	1.2	3				2,200
2GS1.3	1.3	3				4,350
2GS1.4	1.4	3				4,350
2GS1.5 × 4	1.5	3.75				2,320
2GS1.6	1.6	4				4,350
2GS1.7	1.7	4				4,350
2GS1.8	1.8	5				2,200
2GS1.9	1.9	5				4,350
2GS2 × 4	2	6				2,320
2GS2.1	2.1	6				5,140
2GS2.2	2.2	6				5,140
2GS2.3	2.3	6				5,140
2GS2.4	2.4	6.25				5,140
2GS2.5 × 4	2.5	6.25				2,320
2GS2.6	2.6	7				5,140
2GS2.7	2.7	7				5,140
2GS2.8	2.8	7				4,400
2GS2.9	2.9	7				5,140
2GS3 × 6	3	7.5	45	6		2,900
2GS3.1	3.1	8				5,230
2GS3.2	3.2	8				5,230
2GS3.3	3.3	10				5,230
2GS3.4	3.4	10				4,400
2GS3.5	3.5	10				5,230
2GS3.6	3.6	11				5,230
2GS3.7	3.7	11				5,230
2GS3.8	3.8	11				5,230
2GS3.9	3.9	11				5,230
2GS4 × 6	4	13				3,040
2GS4.1	4.1	13				5,660
2GS4.2	4.2	13	50	6		5,660
2GS4.3	4.3	13				5,660
2GS4.4	4.4	13				5,660
2GS4.5	4.5	13				5,000
2GS4.6	4.6	13				5,660
2GS4.7	4.7	13				5,660
2GS4.8	4.8	13				5,660
2GS4.9	4.9	13				5,660
2GS5	5	16				3,270
2GS5.1	5.1	16				5,880
2GS5.2	5.2	16				5,880
2GS5.3	5.3	16				5,880
2GS5.4	5.4	16				5,880
2GS5.5	5.5	16				5,200
2GS5.6	5.6	16				5,880
2GS5.7	5.7	16				5,880
2GS5.8	5.8	16				5,880
2GS5.9	5.9	16				5,880
2GS6	6	16				3,400
2GS7 × 8	7	16	60	8		6,590

単位 (Unit) : mm

商品記号 Code	外径 Dc	刃長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 (円) Price (¥)
2GS8	8	19	60	8	●	5,020
2GS9 × 10	9	22	70	10		8,820
2GS10	10	22	75	12		6,190
2GS11 × 12	11	26		12		11,500
2GS12	12	26		12		8,340
2GS13	13	26	90	16		17,600
2GS14	14	32		16		19,600
2GS15	15	32		16		24,800
2GS16	16	32	100	20		25,100
2GS18	18	38		20		38,900
2GS20	20	38		20		42,400

単位 (Unit) : mm

商品記号 Code	外径 Dc	刃長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 (円) Price (¥)
2GS0.5	0.5	1.25	38	3	●	2,590
2GS1	1	2.5				2,320
2GS1.5	1.5	3.75				2,320
2GS2	2	5				2,320
2GS2.5	2.5	6.25				2,320
2GS3	3	7.5				2,900
2GS4	4	11	45	4		3,040

外径 Dc (mm)		許容差 Tolerance (mm)
を超え Above	以下 Up to	
	3	0 ~ 0.015
3	12	0 ~ 0.020
12		0 ~ 0.030

新商品

超硬ドリル

ハイスドリル

タップ

超硬
エンドミル

ハイス
エンドミル

切断工具

バック・
セット商品
その他

精密工具

技術資料
索引

◎:最適 Excellent ○:適用 Good ×:不適 Not Used -:推奨しません Not recommended