


ティー

● ミリサイズ




品番	適用 チューブ 外径 (mm)	T ねじ サイズ (R)	L1 (mm)	L2 (mm)	L4 (mm)	A (mm)	F チューブ 挿入長さ (mm)	H1 二面幅 (mm)	H2 二面幅 (mm)	d1 (mm)	最小内径 (mm)	有効 断面積 (mm ²)	質量 (g)
CP-T4-R1/8	4	R1/8	26.8	18.0	24.9	8.0	18	10.0	12.0	2.8	2.8	3.0	4.0
CP-T6-R1/8	6	R1/8	29.3	22.0	30.1	12.0	19	12.0	14.0	5.0	5.0	10.0	5.0
CP-T6-R1/4	6	R1/4	29.3	22.0	30.1	12.0	19	12.0	14.0	5.0	5.0	10.0	5.0
CP-T8-R1/8	8	R1/8	36.0	20.5	30.0	10.0	22	9.5	16.5	6.0	6.0	19.5	6.0
CP-T8-R1/4	8	R1/4	36.0	24.0	33.5	13.0	22	9.5	16.5	6.0	5.8	19.5	6.0
CP-T10-R1/4	10	R1/4	45.0	28.5	39.5	12.0	29	12.0	19.0	8.0	8.0	30.0	9.0
CP-T10-R3/8	10	R3/8	45.0	29.0	40.0	13.5	29	12.0	19.0	8.0	8.0	30.0	10.0
CP-T12-R3/8	12	R3/8	50.1	31.0	43.4	13.5	29	13.5	21.5	9.9	9.9	46.0	12.0
CP-T12-R1/2	12	R1/2	50.1	33.0	45.4	15.5	29	13.5	21.5	9.9	9.9	46.0	14.0

● インチサイズ

品番	適用 チューブ 外径 (inch)	T ねじ サイズ (R)	L1 (mm)	L2 (mm)	L4 (mm)	A (mm)	F チューブ 挿入長さ (mm)	H1 二面幅 (mm)	H2 二面幅 (mm)	d1 (mm)	最小内径 (mm)	有効 断面積 (mm ²)	質量 (g)
CP-T1/4-R1/8	1/4	R1/8	29.6	22.0	30.1	12.0	19	12.0	14.0	5.0	5.0	12.0	5.0
CP-T1/4-R1/4	1/4	R1/4	29.6	22.0	30.1	12.0	19	12.0	14.0	5.0	5.0	12.0	5.0
CP-T3/8-R1/4	3/8	R1/4	44.1	28.5	39.5	12.0	28	12.0	19.0	8.0	8.0	29.0	9.0
CP-T3/8-R3/8	3/8	R3/8	44.0	29.0	40.0	13.5	28	12.0	19.0	8.0	8.0	29.0	10.0
CP-T1/2-R3/8	1/2	R3/8	50.6	31.0	43.7	13.5	29	13.5	22.0	9.9	9.9	53.0	12.0
CP-T1/2-R1/2	1/2	R1/2	50.6	33.0	45.7	15.5	29	13.5	22.0	9.9	9.9	53.0	14.0

サービスティー

● ミリサイズ



品番	適用 チューブ 外径 (mm)	T ねじ サイズ (R)	L2 (mm)	L6 (mm)	L7 (mm)	A (mm)	F チューブ 挿入長さ (mm)	H1 二面幅 (mm)	H2 二面幅 (mm)	d1 (mm)	最小内径 (mm)	有効 断面積 (mm ²)	質量 (g)
CP-ST4-R1/8	4	R1/8	18.0	26.8	44.8	8.0	18	10.0	12.0	2.8	2.8	3.0	4.0
CP-ST6-R1/8	6	R1/8	22.0	29.1	51.1	12.0	19	12.0	14.0	5.0	5.0	10.0	5.0
CP-ST6-R1/4	6	R1/4	22.0	29.1	51.1	12.0	19	12.0	14.0	5.0	5.0	10.0	5.0
CP-ST8-R1/8	8	R1/8	21.0	36.5	57.5	10.0	22	9.5	16.5	6.0	6.0	19.5	6.0
CP-ST8-R1/4	8	R1/4	23.5	36.5	60.0	13.0	22	9.5	16.5	6.0	6.0	19.5	6.0
CP-ST10-R1/4	10	R1/4	28.0	45.3	73.3	12.0	29	12.0	19.0	8.0	8.0	30.0	9.0
CP-ST10-R3/8	10	R3/8	30.0	45.3	75.3	13.5	29	12.0	19.0	8.0	8.0	30.0	9.0
CP-ST12-R3/8	12	R3/8	30.3	50.2	80.5	13.5	29	13.5	21.5	9.9	9.9	46.0	12.0
CP-ST12-R1/2	12	R1/2	32.5	50.2	82.7	15.5	29	13.5	21.5	9.9	9.9	46.0	14.0

● インチサイズ

品番	適用 チューブ 外径 (inch)	T ねじ サイズ (R)	L2 (mm)	L6 (mm)	L7 (mm)	A (mm)	F チューブ 挿入長さ (mm)	H1 二面幅 (mm)	H2 二面幅 (mm)	d1 (mm)	最小内径 (mm)	有効 断面積 (mm ²)	質量 (g)
CP-ST1/4-R1/8	1/4	R1/8	22.0	29.4	51.4	12.0	19	12.0	14.0	5.0	5.0	12.0	5.0
CP-ST1/4-R1/4	1/4	R1/4	22.0	29.4	51.4	12.0	19	12.0	14.0	5.0	5.0	12.0	5.0
CP-ST3/8-R1/4	3/8	R1/4	28.0	44.4	72.4	12.0	28	12.0	19.0	8.0	8.0	29.0	9.0
CP-ST3/8-R3/8	3/8	R3/8	30.0	44.4	74.4	13.5	28	12.0	19.0	8.0	8.0	29.0	9.0
CP-ST1/2-R3/8	1/2	R3/8	30.3	50.7	81.0	13.5	29	13.5	22.0	9.9	9.9	53.0	12.0
CP-ST1/2-R1/2	1/2	R1/2	32.5	50.7	83.2	16.0	29	13.5	22.0	9.9	9.9	53.0	14.0