



KLD

キーレスドリルチャック

Keyless Drill Chuck



商品コード Code	型式 Model	d	D	L1	L2	kg	-	スパナ Spanner
2680 01065070	BT30 -KLD6.5 -70	0.5 ~ 6.5	34	76	70	1.0	36,250	FC6.5LC
2680 01130090	-KLD13 -90	0.5 ~ 13	50	102	90	1.5	38,750	FC13LC
2680 03065075	BT40 -KLD6.5 -75	0.5 ~ 6.5	34	81	75	1.2	38,610	FC6.5LC
2680 03065105	-105	0.5 ~ 6.5	34	111	105	1.4	38,610	FC6.5LC
2680 03065150	-150	0.5 ~ 6.5	34	156	150	1.6	40,950	FC6.5LC
2680 03130095	-KLD13 -95	0.5 ~ 13	50	107	95	1.7	42,250	FC13LC
2680 03130105	-105	0.5 ~ 13	50	117	105	1.9	42,250	FC13LC
2680 03130150	-150	0.5 ~ 13	50	162	150	2.5	43,550	FC13LC
2680 05065085	BT50 -KLD6.5 -85	0.5 ~ 6.5	34	91	85	3.8	43,130	FC6.5LC
2680 05065105	-105	0.5 ~ 6.5	34	111	105	3.9	43,130	FC6.5LC
2680 05065150	-150	0.5 ~ 6.5	34	156	150	4.1	44,850	FC6.5LC
2680 05130105	-KLD13 -105	0.5 ~ 13	50	117	105	4.3	47,960	FC13LC
2680 05130135	-135	0.5 ~ 13	50	147	135	4.6	47,960	FC13LC
2680 05130165	-165	0.5 ~ 13	50	177	165	5.0	49,450	FC13LC



商品コード Code	型式 Model	d	D	d1	d2	L1	L2	L3	kg	-	スパナ Spanner
2684 20065065	ST20 -KLD6.5 -65	0.5 ~ 6.5	34	20	32	84	78	65	0.4	29,500	FC6.5LC
2684 25065065	ST25 -KLD6.5 -65	0.5 ~ 6.5	34	25	32	64	58	65	0.5	29,500	FC6.5LC
2684 25465065	ST25.4 -KLD6.5 -65	0.5 ~ 6.5	34	25.4	32	64	58	65	0.5	29,500	FC6.5LC
2684 32065065	ST32 -KLD6.5 -65	0.5 ~ 6.5	34	32	-	54	48	65	0.7	30,680	FC6.5LC
2684 32130065	-KLD13 -65	0.5 ~ 13	50	32	48	86	74	65	1.2	33,040	FC13LC
2684 38065075	ST38.1 -KLD6.5 -75	0.5 ~ 6.5	34	38.1	-	54	48	75	1.0	30,680	FC6.5LC
2684 38130075	-KLD13 -75	0.5 ~ 13	50	38.1	48	86	74	75	1.5	33,040	FC13LC
2684 40065075	ST40 -KLD6.5 -75	0.5 ~ 6.5	34	40	-	54	48	75	1.0	30,680	FC6.5LC
2684 40130075	-KLD13 -75	0.5 ~ 13	50	40	48	86	74	75	1.5	33,040	FC13LC
2684 42065080	ST42 -KLD6.5 -80	0.5 ~ 6.5	34	42	-	54	48	80	1.1	30,680	FC6.5LC
2684 42130080	-KLD13 -80	0.5 ~ 13	50	42	48	86	74	80	1.7	33,040	FC13LC
2684 50065085	ST50 -KLD6.5 -85	0.5 ~ 6.5	34	50	-	54	48	85	1.6	31,860	FC6.5LC
2684 50130085	-KLD13 -85	0.5 ~ 13	50	50	-	76	64	85	2.2	34,220	FC13LC

専用スパナ (別売) Spanner (option)

型式 Model	商品コード Code	-
FC6.5LC	2685 00000065	1,200
FC13LC	2685 00000130	1,500

ご注文例 Ordering Example

BT40 - KLD13 - 105

シャンクサイズ 最大把握径 突き出し長さ(L2)
Shank size Max. chucking dia. Projection length