




※ h7 公差は N38 参照

刃先交換ヘッド

Fig 1

刃先交換ヘッド MFS 型 刃径 $\phi 12.0 \sim 21.5\text{mm}$ 寸法(mm)

刃径 DC	在庫	型番	肩部長 LF	先端 PL	適用ホルダ	Fig
12.0	●	SMDT 1200 MFS	7.1	—	SMDH120□	1
12.5	●	1250 MFS	7.2	—	SMDH125□	1
13.0	●	1300 MFS	7.5	—	SMDH130□	1
13.5	●	SMDT 1350 MFS	—	—	—	1
14.0	●	1400 MFS	7.9	—	SMDH140□	1
14.5	●	1450 MFS	—	—	—	1
15.0	●	SMDT 1500 MFS	8.3	—	SMDH150□	1
15.5	●	1550 MFS	—	—	—	1
16.0	●	SMDT 1600 MFS	8.8	—	SMDH160□	1
16.5	●	1650 MFS	—	—	—	1
17.0	●	SMDT 1700 MFS	9.3	—	SMDH170□	1
17.5	●	1750 MFS	—	—	—	1
18.0	●	SMDT 1800 MFS	9.8	—	SMDH180□	1
18.5	●	1850 MFS	—	—	—	1
19.0	●	SMDT 1900 MFS	10.2	—	SMDH190□	1
19.5	●	1950 MFS	—	—	—	1
20.0	●	SMDT 2000 MFS	10.7	—	SMDH200□	1
20.5	●	2050 MFS	—	—	—	1
21.0	●	SMDT 2100 MFS	11.2	—	SMDH210□	1
21.5	●	2150 MFS	—	—	—	1

材種 ACX70


推奨切削条件 J104 適用ホルダ J106、J107

刃先交換ヘッド MFS 型 刃径 $\phi 22.0 \sim 30.0\text{mm}$ 寸法(mm)

刃径 DC	在庫	型番	肩部長 LF	先端 PL	適用ホルダ	Fig
22.0	●	SMDT 2200 MFS	—	—	—	1
22.5	●	2250 MFS	11.2	—	SMDH220□	1
23.0	●	SMDT 2300 MFS	11.2	—	SMDH230□	1
23.5	●	2350 MFS	—	—	—	1
24.0	●	SMDT 2400 MFS	11.3	—	SMDH240□	1
24.5	●	2450 MFS	—	—	—	1
25.0	●	SMDT 2500 MFS	11.7	—	SMDH250□	1
25.5	●	2550 MFS	—	—	—	1
26.0	●	SMDT 2600 MFS	12.2	—	SMDH260□	1
26.5	●	2650 MFS	—	—	—	1
27.0	●	SMDT 2700 MFS	12.7	—	SMDH270□	1
27.5	●	2750 MFS	—	—	—	1
28.0	●	SMDT 2800 MFS	13.2	—	SMDH280□	1
28.5	●	2850 MFS	—	—	—	1
29.0	●	SMDT 2900 MFS	13.6	—	SMDH290□	1
29.5	●	2950 MFS	—	—	—	1
30.0	●	SMDT 3000 MFS	14.1	—	SMDH300□	1

材種 ACX70

MFS型の穴底形状

穴
あ
け

J

ソ
リ
ッド交
換
式イ
ン
サ
ー
トリ
ー
マろ
う
付
けそ
の
他