




ブランチエルボユニオン:KGLU


〈M5の場合〉



適用チューブ 外径mm	接続ねじ M R	型式	H (六角 対辺)	φD	L1	L2	L3	※A	M	P	Q1	Q2	有効断面積 mm ²		質量 g
													ナイロン	ウレタン	
4	M5×0.8	KGLU04-M5	11	10.4	18.5	24	29.5	25.5	16	10.4	18.5	10	4.3	4.1	10
	1/8	KGLU04-01	25.6			31.1	27.5	6.0					4.1	12	
	1/4	KGLU04-02	30			35.5	30	21							
6	M5×0.8	KGLU06-M5	13	12.8	21	26.5	33	29.5	17	12.8	20.5	12	4.3	4.3	13
	1/8	KGLU06-01	28.6			35.1	32	13.9					11.0	15	
	1/4	KGLU06-02	32.5			39	33.5							22	
	3/8	KGLU06-03	33.9			40.4	35							35	
8	1/8	KGLU08-01	17	15.2	24	33.1	40.6	38	18.5	15.2	24.5	14	26.3	18.2	27
	1/4	KGLU08-02				36.5	44	38.5							35
	3/8	KGLU08-03				36.9	44.4	39							41
10	1/4	KGLU10-02	19	18.5	27	39.5	49	43.5	21	18.5	28	16	40.8	29.0	42
	3/8	KGLU10-03				39.9	49.4	44							64
	1/2	KGLU10-04				43.6	53.1	45.5							57
12	1/4	KGLU12-02	22	20.9	29	42	52.5	47	22	20.9	30	18	57.2	45.2	58
	3/8	KGLU12-03				42.4	52.9	47.5							65
	1/2	KGLU12-04				45.6	56.1	49							65


※Rねじのねじ込み後の参考寸法

〈Rの場合〉



ユニバーサルエルボユニオン:KGV


〈M5の場合〉



適用チューブ 外径mm	接続ねじ M R	型式	H (六角 対辺)	φD1	φD2	L1	L2	L3	※A	M	有効断面積 mm ²		質量 g
											ナイロン	ウレタン	
4	M5×0.8	KGV04-M5	8	10.4	9.8	20.5	11	18.5	15	16	2.9	2.9	6
	1/8	KGV04-01			13.4	22	13.6	25.6	22.5		3.8	3.8	14
6	M5×0.8	KGV06-M5	8	12.8	9.8	23.5	12	18.5	15	17	7.5	5.9	7
	1/8	KGV06-01			13.4	24	13.6	25.6	22.5				15
	1/4	KGV06-02			15.3	23.5	18	30.5	25				26
8	1/8	KGV08-01	12	15.2	17.6	28.5	14.6	27.6	24.5	18.5	16	11.2	24
	1/4	KGV08-02			18	31	25.5	30	20.5				30
	3/8	KGV08-03			20.6	27.5	19.4	35.4	30				47
10	1/4	KGV10-02	14	18.5	20.6	31	19	35	29.5	21	27	20.3	40
	3/8	KGV10-03			20.6	31	19.4	35.4	30				49
12	3/8	KGV12-03	17	20.9	25.2	34	20.9	37.4	32	22	39	30.8	63
	1/2	KGV12-04			25.2	34	24.1	40.6	33.5				80

※Rねじのねじ込み後の参考寸法

〈Rの場合〉



KQ2

KQB2

KS
KX

KM

KF

M

H/DL
L/LL

KC

KK

KK130

DM

KDM

KB

KR

KA

KQG2

KQ2-G

KG

KFG2

MS

KF□
KQ□

KQ
X1744

KKA

KP

LQ

MQR

T

IDK