

品名 품명 Model	外径 외경(mm) Outer Dia.	内径 내경(mm) Inner Dia.	自由長 자유장(mm) Free length	密着長 밀착장(mm) Solid Length	定数 정수(kgf/mm) spring constant	30万 (0.3million)		50万 (0.5million)		100万 (1million)	
						変形量 변형량(mm) Deflection	荷重 하중(kgf) Load	変形量 변형량(mm) Deflection	荷重 하중(kgf) Load	変形量 변형량(mm) Deflection	荷重 하중(kgf) Load
SR 10.5×15	10.5	6	15	6	1.07	7.5	8	6.75	7.2	6	6.4
20			20	8	0.80	10		9		8	
25			25	10	0.64	12.5		11.25		10	
30			30	12	0.53	15		13.5		12	
35			35	14	0.46	17.5		15.75		14	
40			40	16	0.40	20		18		16	
45			45	18	0.36	22.5		20.25		18	
50			50	20	0.32	25		22.5		20	
55			55	22	0.29	27.5		24.75		22	
60			60	24	0.27	30		27		24	
65			65	26	0.25	32.5		29.25		26	
70			70	28	0.23	35		31.5		28	
75			75	30	0.21	37.5		33.75		30	
80			80	32	0.20	40		36		32	
SR 12.5×15	12.5	7	15	6	1.20	7.5	9	6.75	8.1	6	7.2
20			20	8	0.90	10		9		8	
25			25	10	0.72	12.5		11.25		10	
30			30	12	0.60	15		13.5		12	
35			35	14	0.51	17.5		15.75		14	
40			40	16	0.45	20		18		16	
45			45	18	0.40	22.5		20.25		18	
50			50	20	0.36	25		22.5		20	
55			55	22	0.33	27.5		24.75		22	
60			60	24	0.30	30		27		24	
65			65	26	0.28	32.5		29.25		26	
70			70	28	0.26	35		31.5		28	
75			75	30	0.24	37.5		33.75		30	
80			80	32	0.23	40		36		32	
90	90	36	0.20	45	40.5	36					
100	100	40	0.18	50	45	40					
SR 14.5×20	14.5	9	20	8	1.11	10	11	9	10	8	9
25			25	10	0.89	12.5		11.3		10	
30			30	12	0.74	15		13.5		12	
35			35	14	0.64	17.5		15.8		14	
40			40	16	0.56	20		18		16	
45			45	18	0.49	22.5		20.3		18	
50			50	20	0.44	25		22.5		20	
55			55	22	0.40	27.5		24.8		22	
60			60	24	0.37	30		27		24	
65			65	26	0.34	32.5		29.3		26	
70			70	28	0.32	35		31.5		28	
75			75	30	0.30	37.5		33.8		30	
80			80	32	0.28	40		36		32	
90			90	36	0.25	45		40.5		36	
100	100	40	0.22	50	45	40					
125	125	50	0.18	62.5	56.3	50					