


## ねじ込みタイプアダプター

- Material : Plated steel
- 材質 : SS(三価クロメートメッキ)


### M (ブッシング)



SUSは受注生産

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	Lmm	HEXmm
6×3	R ¼	Rc ¼	7	13	20	17
9×3	R ⅜	Rc ¼	8	15	23	19
9×6	R ⅜	Rc ¼	8	15	23	19
12×3	R ½	Rc ¼	9	18	27	24
12×6	R ½	Rc ¼	9	18	27	24
12×9	R ½	Rc ⅜	9	18	27	24
19×6	R ¾	Rc ¼	10	20	30	30
19×9	R ¾	Rc ⅜	10	20	30	30
19×12	R ¾	Rc ½	10	20	30	30
25×9	R 1	Rc ⅜	11	22	33	36
25×12	R 1	Rc ½	11	22	33	36
25×19	R 1	Rc ¾	11	22	33	36


### NC (オスメスニップル)



\*印及びSUSは受注生産

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	dφmm	Lmm	HEXmm
3	R ⅙	Rc ⅙	15	10	4.0	25	14
6	R ¼	Rc ¼	17	13	5.5	30	19
9	R ⅜	Rc ⅜	19	15	7.0	34	22
12	R ½	Rc ½	22	18	10.0	40	27
19	R ¾	Rc ¾	25	20	16.0	45	36
25	R 1	Rc 1	27	22	21.5	49	41
* 32	R 1¼	Rc 1¼	30	25	27.5	55	50
* 38	R 1½	Rc 1½	30	25	33.0	55	60
* 50	R 2	Rc 2	36	30	44.0	66	70


### NC (異径オスメスニップル)



SUSは受注生産

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	dφmm	Lmm	HEXmm
3×6	R ⅙	Rc ¼	17	10	4.0	27	19
6×9	R ¼	Rc ⅜	19	13	5.5	32	22
9×12	R ⅜	Rc ½	22	15	7.0	37	27
12×19	R ½	Rc ¾	25	18	10.0	43	36
19×25	R ¾	Rc 1	27	20	16.0	47	41

### OML-90 (オスメス 90° エルボ)



SUSは受注生産

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	Cmm	dφmm	Emm
3	Rc ⅙	R ⅙	12.0	21	10	4.5	14
6	Rc ¼	R ¼	16.0	26	15	6.0	19
9	Rc ⅜	R ⅜	17.5	32	19	8.0	22
12	Rc ½	R ½	26.0	41	24	10.0	30
19	Rc ¾	R ¾	30.0	46	28	16.0	36
25	Rc 1	R 1	35.0	54	32	21.5	41

(注意)予告なしに、改善(品質・性能・価格等)の為寸法等を変更する事がありますのでご了承ください。