

スーパー超硬バー

SUPER CARBIDE BURS

■シャंक径 a φ6mm ★印はオール超硬



(mm)

品番 (W.cut)	品番 (S.cut)	b	ℓ	L	メーカー希望小売価格
SB1C01★	SB1C01S★	3	16	50	2,540
SB1C02★	SB1C02S★	4	16	50	2,540
SB1C03★	SB1C03S★	5	16	50	2,540
SB1C04★	SB1C04S★	6	16	50	2,540
SB1C05	SB1C05S	8	19	63	3,320
SB1C06	SB1C06S	9.5	19	63	3,410
SB1C07	SB1C07S	11	25	69	5,190
SB1C08	SB1C08S	12.7	25	69	5,580
SB1C09	SB1C09S	16	25	69	7,820
SB1C10	SB1C10S	19	25	69	11,640



(mm)

品番 (W.cut)	品番 (S.cut)	b	ℓ	L	メーカー希望小売価格
SB1C01E★	SB1C01ES	3	16	50	2,740
SB1C02E★	SB1C02ES★	4	16	50	2,740
SB1C03E★	SB1C03ES★	5	16	50	2,740
SB1C04E★	SB1C04ES★	6	16	50	2,740
SB1C05E	SB1C05ES	8	19	63	3,640
SB1C06E	SB1C06ES	9.5	19	63	3,920
SB1C07E	SB1C07ES	11	25	69	5,700
SB1C08E	SB1C08ES	12.7	25	69	6,100
SB1C09E	SB1C09ES	16	25	69	8,610
SB1C10E	SB1C10ES	19	25	69	12,820



(mm)

品番 (W.cut)	品番 (S.cut)	b	ℓ	L	メーカー希望小売価格
SB2C01★	SB2C01S	3	16	50	2,890
SB2C02★	SB2C02S★	4	16	50	2,890
SB2C03★	SB2C03S★	5	16	50	2,890
SB2C04★	SB2C04S★	6	16	50	2,890
SB2C05	SB2C05S	8	19	63	3,810
SB2C06	SB2C06S	9.5	19	63	3,960
SB2C07	SB2C07S	11	25	69	5,670
SB2C08	SB2C08S	12.7	25	69	6,240
SB2C09	SB2C09S	16	25	69	8,760
SB2C10	SB2C10S	19	25	69	12,590



(mm)

品番 (W.cut)	品番 (S.cut)	b	ℓ	L	メーカー希望小売価格
SB3C01★	SB3C01S	3	12.7	50	3,060
SB3C02★	SB3C02S★	6	16	50	3,060
SB3C03	SB3C03S	9.5	19	63	3,890
SB3C04	SB3C04S	11	25	69	5,380
SB3C05	SB3C05S	12.7	25	69	5,730
SB3C06	SB3C06S	16	25	69	8,830
SB3C07	SB3C07S	19	25	69	11,640



(mm)

品番 (W.cut)	品番 (S.cut)	b	ℓ	L	メーカー希望小売価格
SB4C01★	SB4C01S★	6	16	50	3,060
SB4C02	SB4C02S	8	19	63	3,710
SB4C03	SB4C03S	9.5	19	63	4,130
SB4C04	SB4C04S	12.7	25	69	5,640
SB4C05	SB4C05S	16	25	69	8,760
SB4C06	SB4C06S	19	25	69	11,640



(mm)

品番 (W.cut)	品番 (S.cut)	b	ℓ	L	メーカー希望小売価格
SB5C01★	SB5C01S★	6 ^{2R}	12.7	50	3,130
SB5C02★	SB5C02S★	6 ¹⁴	19	50	3,130
SB5C03★	SB5C03S★	6 ¹²	25	50	3,130
SB5C04	SB5C04S	9.5 ^{2R}	16	63	4,840
SB5C05	SB5C05S	12.7 ^{2R}	22	69	6,420
SB5C06	SB5C06S	16 ^{3R}	25	73	6,950



(mm)

品番 (W.cut)	品番 (S.cut)	b	ℓ	L	メーカー希望小売価格
SB6C01★	SB6C01S★	6	9.5	50	3,540
SB6C02	SB6C02S	9.5	16	60	3,960
SB6C03	SB6C03S	12.7	22	66	5,800
SB6C04	SB6C04S	16	25	69	9,030
SB6C05	SB6C05S	19	25	69	12,110

14°



(mm)

品番 (W.cut)	品番 (S.cut)	b	ℓ	L	メーカー希望小売価格
SB7C01★	SB7C01S★	6	16	50	3,130
SB7C02	SB7C02S	8	22	69	4,130
SB7C03	SB7C03S	9.5	27	74	4,840
SB7C04	SB7C04S	12.7	28	76	6,470
SB7C05	SB7C05S	16	30	77	12,110
SB7C06	SB7C06S	19	38	85	17,560



(mm)

品番 (W.cut)	品番 (S.cut)	b	ℓ	L	メーカー希望小売価格
SB8C01	SB8C01S	3	2.5	50	2,700
SB8C02★	SB8C02S★	5	4	50	2,700
SB8C03★	SB8C03S★	6	5	50	2,700
SB8C04	SB8C04S	8	6.4	50	2,910
SB8C05	SB8C05S	9.5	8	52	3,260
SB8C06	SB8C06S	11	9.5	54	3,780
SB8C07	SB8C07S	12.7	11	55	4,390
SB8C08	SB8C08S	16	14	58	6,080
SB8C09	SB8C09S	19	16	62	8,380

90°



(mm)

品番 (W.cut)	品番 (S.cut)	b	ℓ	L	メーカー希望小売価格
SB49C01★	SB49C01S★	6	3	50	2,700
SB49C02	SB49C02S	9.5	4.7	52	3,540
SB49C03	SB49C03S	12.7	6.3	54	4,320
SB49C04	SB49C04S	16	8	57	6,420
SB49C05	SB49C05S	19	9.5	58	8,410

60°



(mm)

品番 (W.cut)	品番 (S.cut)	b	ℓ	L	メーカー希望小売価格
SB50C01★	SB50C01S★	6	4	50	2,700
SB50C02	SB50C02S	9.5	8	55	3,540
SB50C03	SB50C03S	12.7	11	58	4,320
SB50C04	SB50C04S	16	14.5	61	6,420
SB50C05	SB50C05S	19	17.5	65	8,410



(mm)

品番 (W.cut)	品番 (S.cut)	b	ℓ	L	メーカー希望小売価格
SB51C01	SB51C01S	8	19	63	4,100
SB51C02	SB51C02S	12.7	32	76	8,320
SB51C03	SB51C03S	16	36	80	12,820
SB51C04	SB51C04S	19	41	85	16,300



(mm)

品番 (W.cut)	品番 (S.cut)	b	ℓ	L	メーカー希望小売価格
SB52C01★	SB52C01S★	6 ¹⁰	8	50	3,020
SB52C02	SB52C02S	9.5 ¹³	9.5	53	4,390
SB52C03	SB52C03S	12.7 ¹⁶	12.7	57	6,210
SB52C04	SB52C04S	16 ¹⁸	19	63	8,090
SB52C05	SB52C05S	19 ²⁰	16	60	9,140

マイクロエアグラインダー&スーパー超硬バー

MICRO AIR GRINDERS & SUPER CARBIDE BURS