


**VU** 管形ストレートタイプ (大気開放)

RoHS対応



単位: mm

形 式	チューブ外径 D	R	A	B	L	C	ノズル径 (mm)	到達真空度 (-kPa)	吸入流量 (ℓ/min[ANR])	消費流量 (ℓ/min[ANR])	質量 (g)	CAD ファイル名
VUH05-M54A	4	M5 × 0.8	3	50	47	10.9	0.5	90	7	11.5	18	VU_05-M54A
VUH05-M56A	6			51.1	48.1	11.7					17	VU_05-M56A
VUH05-M64A	4	M6 × 1	3.4	50.5	47.1	10.9					18	VU_05-M64A
VUH05-M66A	6			51.6	48.2	11.7					17	VU_05-M66A
VUH05-014A	4	R1/8	8	54	50	10.9					20	VU_05-014A
VUH05-016A	6			55.1	51.1	11.7					20	VU_05-016A
VUH07-M54A	4	M5 × 0.8	3	56.8	53.8	10.9	0.7	92	12.5	23	19	VU_07-M54A
VUH07-M56A	6			57.6	54.6	11.7					18	VU_07-M56A
VUH07-M64A	4	M6 × 1	3.4	57.3	53.9	10.9					19	VU_07-M64A
VUH07-M66A	6			58.1	54.7	11.7					19	VU_07-M66A
VUH07-014A	4	R1/8	8	60.8	56.8	10.9					21	VU_07-014A
VUH07-016A	6			61.6	57.6	11.7					21	VU_07-016A
VUL05-M54A	4	M5 × 0.8	3	50	47	10.9	0.5	66	12	11.5	18	VU_05-M54A
VUL05-M56A	6			51.1	48.1	11.7					17	VU_05-M56A
VUL05-M64A	4	M6 × 1	3.4	50.5	47.1	10.9					18	VU_05-M64A
VUL05-M66A	6			51.6	48.2	11.7					17	VU_05-M66A
VUL05-014A	4	R1/8	8	54	50	10.9					20	VU_05-014A
VUL05-016A	6			55.1	51.1	11.7					20	VU_05-016A
VUL07-M54A	4	M5 × 0.8	3	56.8	53.8	10.9	0.7		20	23	19	VU_07-M54A
VUL07-M56A	6			57.6	54.6	11.7					18	VU_07-M56A
VUL07-M64A	4	M6 × 1	3.4	57.3	53.9	10.9					19	VU_07-M64A
VUL07-M66A	6			58.1	54.7	11.7					18	VU_07-M66A
VUL07-014A	4	R1/8	8	60.8	56.8	10.9					21	VU_07-014A
VUL07-016A	6			61.6	57.6	11.7					21	VU_07-016A
VUE07-M54A	4	M5 × 0.8	3	56.8	53.8	10.9	0.7	90	10	17	19	VU_07-M54A
VUE07-M56A	6			57.6	54.6	11.7					19	VU_07-M56A
VUE07-M64A	4	M6 × 1	3.4	57.3	53.9	10.9					22	VU_07-M64A
VUE07-M66A	6			58.1	54.7	11.7					22	VU_07-M66A
VUE07-014A	4	R1/8	8	60.8	56.8	10.9					22	VU_07-014A
VUE07-016A	6			61.6	57.6	11.7					21	VU_07-016A

※. テーパネジタイプのL寸法は、ねじ締付け後の参考寸法です。

※. M5、M6ネジは、六角対辺部がローレットになっております。また、Hex. 12は、01(R1/8)ネジの場合です。