


■ ネジ⇄チューブの接続

KJNC エルボ カバー付

RoHS対応

557
P.521

CAD
2D & 3D



単位：mm

形 式	チューブ外径 øD1	チューブ外径 øD2	R	A	B		L1		L2	øP1	øP2	øP3	C1	C2	E	対辺 H	質量 (g)	CAD ファイル名
					max.	min.	max.	min.										
KJNC4-M5-□	4	6	M5×0.8	3	32.6	29.9	29.6	26.9	8.1	12.5	10.4	12	17.6	15	22.8	11	27	KJNC4-M5
KJNC4-01-□			R1/8	8.5	45.1	38.7	41.1	34.7	12.1						24.8	14	45	KJNC4-01
KJNC6-M5-□	6	8	M5×0.8	3	32.6	29.9	29.6	26.9	8.1	12.5	12.4	12	19.5	16	24.1	11	27	KJNC6-M5
KJNC6-01-□			R1/8	8.5	45.1	38.7	41.1	34.7	12.1						26.1	14	45	KJNC6-01
KJNC6-02-□			R1/4	11.1	53.8	46.7	47.8	40.7	15	14.5	19	22.5	19.5	16	27.6	17	72	KJNC6-02
KJNC6-03-□			R3/8	12.6	60.2	51.9	53.8	45.5	17.4						29.3	21	113	KJNC6-03
KJNC8-01-□	8	10	R1/8	8.5	45.1	38.7	41.1	34.7	12.1	14.5	14.4	16	20.2	17	26.9	14	48	KJNC8-01
KJNC8-02-□			R1/4	11.1	53.8	46.7	47.8	40.7	15						28.4	17	72	KJNC8-02
KJNC8-03-□			R3/8	12.6	60.2	51.9	53.8	45.5	17.4						30.1	21	113	KJNC8-03
KJNC10-02-□	10	12	R1/4	11.1	53.8	46.7	47.8	40.7	15	18.5	18.6	19	23.2	19.5	31.2	17	85	KJNC10-02
KJNC10-03-□			R3/8	12.6	60.2	51.9	53.8	45.5	17.4						33	21	134	KJNC10-03
KJNC10-04-□			R1/2	13.6	63.2	55.6	55	47.5	17.4						35.5	27	194	KJNC10-04
KJNC12-03-□	12	14	R3/8	12.6	60.2	51.9	53.8	45.5	17.4	21.5	21.6	22.5	26.3	23	36.1	21	140	KJNC12-03
KJNC12-04-□			R1/2	13.6	63.2	55.6	55	47.5	17.4						38.6	27	201	KJNC12-04

※.テーパネジタイプのL1、L2寸法は、ねじ締付け後の参考寸法です。

※.形式末尾の□には、シールゴム材質にFKMを希望される場合記号：Fをご記入ください。

519

速度
制御弁

速度制御弁
耐腐蝕用

速度制御弁
クリーン

速度制御弁
耐入パツタ

固定式
速度制御弁

ニードル
弁

ニードル弁
耐腐蝕用

ニードル弁
クリーン

ニードル弁
耐入パツタ