


適合インサート

GBR/L32




本図は右勝手(R)を示す。

| 形番 | CW±0.025 | RE | コーティング | | サーメット | | 超硬 | | CDX | IC | S |
|------------|----------|------|--------|---|--------|---|-------|---|-----|-------|------|
| | | | AH710 | | NS9530 | | KS05F | | | | |
| | | | R | L | R | L | R | L | | | |
| GBR/L32033 | 0.33 | 0.03 | ● | ● | ● | | ● | | 0.8 | 9.525 | 3.18 |
| GBR/L32050 | 0.5 | 0.05 | ● | ● | ● | | ● | | 1.2 | 9.525 | 3.18 |
| GBR/L32075 | 0.75 | 0.05 | ● | ● | ● | ● | ● | | 2 | 9.525 | 3.18 |
| GBR/L32095 | 0.95 | 0.05 | ● | ● | ● | ● | ● | | 2 | 9.525 | 3.18 |
| GBR/L32100 | 1 | 0.05 | ● | ● | ● | ● | ● | | 2 | 9.525 | 3.18 |
| GBR/L32125 | 1.25 | 0.2 | ● | ● | ● | ● | ● | | 2 | 9.525 | 3.18 |
| GBR/L32145 | 1.45 | 0.2 | ● | ● | ● | | ● | | 2 | 9.525 | 3.18 |
| GBR/L32150 | 1.5 | 0.2 | ● | ● | ● | | ● | | 2 | 9.525 | 3.18 |
| GBR/L32200 | 2 | 0.2 | ● | ● | ● | | ● | | 2.5 | 9.525 | 3.18 |
| GBR/L32250 | 2.5 | 0.2 | ● | ● | ● | | ● | | 2.5 | 9.525 | 3.18 |

●：設定アイテム

GBR/L43



本図は右勝手(R)を示す。

| 形番 | CW±0.025 | RE | コーティング | | サーメット | | 超硬 | | CDX | IC | S |
|------------|----------|-----|--------|---|--------|---|-------|---|-----|------|------|
| | | | AH710 | | NS9530 | | KS05F | | | | |
| | | | R | L | R | L | R | L | | | |
| GBR/L43125 | 1.25 | 0.2 | ● | ● | ● | | ● | | 2 | 12.7 | 4.76 |
| GBR/L43145 | 1.45 | 0.2 | ● | ● | ● | | ● | | 2 | 12.7 | 4.76 |
| GBR/L43150 | 1.5 | 0.2 | ● | ● | ● | ● | ● | | 3.5 | 12.7 | 4.76 |
| GBR/L43175 | 1.75 | 0.2 | ● | ● | ● | ● | ● | | 3.5 | 12.7 | 4.76 |
| GBR/L43185 | 1.85 | 0.2 | ● | ● | ● | ● | ● | | 3.5 | 12.7 | 4.76 |
| GBR/L43200 | 2 | 0.2 | ● | ● | ● | ● | ● | | 3.5 | 12.7 | 4.76 |
| GBR/L43230 | 2.3 | 0.2 | ● | ● | ● | ● | ● | | 3.5 | 12.7 | 4.76 |
| GBR/L43250 | 2.5 | 0.3 | ● | ● | ● | | ● | | 5 | 12.7 | 4.76 |
| GBR/L43265 | 2.65 | 0.3 | ● | ● | ● | | ● | | 5 | 12.7 | 4.76 |
| GBR/L43280 | 2.8 | 0.3 | ● | ● | ● | | ● | | 5 | 12.7 | 4.76 |
| GBR/L43300 | 3 | 0.3 | ● | ● | ● | | ● | | 5 | 12.7 | 4.76 |
| GBR/L43330 | 3.3 | 0.3 | ● | ● | ● | | ● | | 5 | 12.7 | 4.76 |
| GBR/L43350 | 3.5 | 0.3 | ● | ● | ● | | ● | | 5 | 12.7 | 4.76 |
| GBR/L43400 | 4 | 0.4 | ● | ● | ● | | ● | | 5 | 12.7 | 4.76 |
| GBR/L43430 | 4.3 | 0.4 | ● | ● | ● | | ● | | 5 | 12.7 | 4.76 |
| GBR/L43450 | 4.5 | 0.4 | ● | ● | ● | | ● | | 5 | 12.7 | 4.76 |

●：設定アイテム