













形式および ツーリング	形番	在庫		寸法(mm)							基準 コーナ r _E	使用インサート	形状
		R	L	h	b	L ₁	L ₂	h ₁	f	f ₂			
外径切削 CTGNR/L  切刃形状記号 G	CTGNR/L2020	●	●	20	20	125	28.5	20	25	-	0.8	TN□□1604□□ 60°△ ▶ 2-79	 本図は右勝手(R)を示す。
	CTGNR/L2525	●	●	25	25	150		25	32				
端面切削 CTFNR/L  切刃形状記号 F	CTFNR/L2020	●	●	20	20	125	22	20	25	-	0.8	TN□□1604□□ 60°△ ▶ 2-79	 本図は右勝手(R)を示す。
	CTFNR/L2525	●	●	25	25	150		25	32				
外径切削 CSBNR/L  切刃形状記号 B	CSBNR/L2020	●	●	20	20	125	31	20	17	-	0.8	SN□□1204□□ 90°□ ▶ 2-69	 本図は右勝手(R)を示す。
	CSBNR/L2525	●	●	25	25	150		25	22				
外径・面取り CSDNN  切刃形状記号 D	CSDNN2020	●	●	20	20	125	32	20	10.0	-	0.8	SN□□1204□□ 90°□ ▶ 2-69	 本図は右勝手(R)を示す。
	CSDNN2525	●	●	25	25	150		25	12.5				
端面切削 CSKNR/L  切刃形状記号 K	CSKNR/L2020	●	●	20	20	125	25	20	25	-	0.8	SN□□1204□□ 90°□ ▶ 2-69	 本図は右勝手(R)を示す。
	CSKNR/L2525	●	●	25	25	150		25	32				
外径・端面・面取り CSSNR/L  切刃形状記号 S	CSSNR/L2020	●	●	20	20	125	31	20	25	-	0.8	SN□□1204□□ 90°□ ▶ 2-69	 本図は右勝手(R)を示す。
	CSSNR/L2525	●	●	25	25	150		25	32				

製品在庫 ●:在庫形番