













形式および ツーリング	形 番	在庫		寸法(mm)								基準 コーナ r _E	使用インサート	形 状		
		R	L	h	b	L ₁	L ₂	h ₁	f	f ₂						
外径切削 CTGPR/L 	CTGPR/L1616H3	●	●	16	16	100	23	16	20	27	20	-	0.8	TP□□1603□□ 60°△>2-130~		
	CTGPR/L2020K3	●	●	20	20	125	27	20	25							
	CTGPR/L2525M3	●	●	25	25	150		25	32							
端面切削 CTFPR/L 	CTFPR/L1616H3	●	●	16	16	100	23	16	20	26	20	25	-	0.8	TP□□1603□□ 60°△>2-130~	
	CTFPR/L2020K3	●	●	20	20	125	26	20	25							
	CTFPR/L2525M3	●	●	25	25	150		25	32							
端面切削 CTCPR/L 	CTCPR/L2020K3			20	20	125	25	20	25	32	25	32	-	0.8	TP□□1603□□ 60°△>2-130~	
	CTCPR/L2525M3	●	●	25	25	150	32	25	32							
	CTCPR/L3232P3			32	32	170	40	32	40							
外径切削 CSBPR/L 	CSBPR/L1616H3	●	●	16	16	100	25	16	13	32	17	22	-	0.8	SP□□0903□□ 90°□>2-116~	
	CSBPR/L2020K4	●	●	20	20	125	32	20	17							
	CSBPR/L2525M4	●	●	25	25	150		25	22							
外径・面取り CSDPN 	CSDPN1616H3	●		16	16	100	26	16	8	34	20	10	-	0.8	SP□□0903□□ 90°□>2-116~	
	CSDPN2020K4	●		20	20	125	34	20	10							
	CSDPN2525M4	●		25	25	150		25	12.5							
端面切削 CSKPR/L 	CSKPR/L1616H3			16	16	100	23	16	20	26	20	25	-	0.8	SP□□0903□□ 90°□>2-116~	
	CSKPR/L2020K4			20	20	125	26	20	25							
	CSKPR/L2525M4			25	25	150		25	32							

製品在庫 ●:在庫形番