


CY3R Series

外形寸法図

両側配管形：φ6～φ63

注) 本図は、スイッチレール付(無記号)を示します。



型式	A	B	C	CB	CR	D	F	G	GP	GW	H	HA	HB	HC	HP	HR	HS	HT	J×E	K
CY3R6	7*	—*	—*	2	0.5	7.6	5.5	3*	20	18.5	19	17	10.5	18	10.5*	17	6	10.5*	M4×0.7×6	7
CY3R10	9	6.5	3.2	2	0.5	12	6.5	4	27	25.5	26	24	14	25	14	24	5	14	M4×0.7×6	9
CY3R15	10.5	8	4.2	2	0.5	16.6*	8	5	33	31.5	32	30	17	31	17	30	8.5	17	M5×0.8×7	14
CY3R20	9	9.5	5.2	3	1	21.6*	9	6	39	37.5	39	36	21	38	24	36	7.5	24	M6×1×8	11
CY3R25	8.5	9.5	5.2	3	1	26.4*	8.5	6	44	42.5	44	41	23.5	43	23.5	41	6.5	23.5	M6×1×8	15
CY3R32	10.5	11	6.5	3	1.5	33.6*	10.5	7	55	53.5	55	52	29	54	29	51	7	29	M8×1.25×10	13
CY3R40	10	11	6.5	5	2	41.6*	13	7	65	63.5	67	62	36	66	36	62	8	36	M8×1.25×10	15
CY3R50	14	14	8.2	5	2	52.4*	17	8.5	83	81.5	85	80	45	84	45	80	9	45	M10×1.5×15	25
CY3R63	15	14	8.2	5	3	65.4*	18	8.5	95	93.5	97	92	51	96	51	90	9.5	51	M10×1.5×15	24

型式	L	LD	M	MM	N	PW	Q	QW	T	TC	W	WP	WS	X	Y	Z
CY3R6	34	3.5	3.5	M3×0.5	3.5	19	60*	10	14.5*	10.5	20	9.5	6	10	35.5	66*
CY3R10	38	3.5	4	M3×0.5	4.5	26	68	14	17.5	14	20	13	8	15	39.5	76
CY3R15	53	4.3	5	M4×0.7	6	32	84	18	19	17	25	16	7	18	54.5	94
CY3R20	62	5.4	5	M4×0.7	7	38	95	17	20.5	20	40	19	7	22	64	107
CY3R25	70	5.4	6	M5×0.8	6.5	43	105	20	21.5	22.5	40	21.5	7	28	72	117
CY3R32	76	7	7	M6×1	8.5	54	116	26	24	28	50	27	7	35	79	130
CY3R40	90	7	8	M6×1	11	64	134	34	26	33	60	32	7	40	93	148
CY3R50	110	8.6	10	M8×1.25	15	82	159	48	30	42	60	41	10	50	113	176
CY3R63	118	8.6	10	M8×1.25	16	94	171	60	32	48	70	47	10	60	121	188

型式	P(配管ポート)		
	無記号	TN*	TF*
CY3R6	M3×0.5*	—	—
CY3R10	M5×0.8	—	—
CY3R15	M5×0.8	—	—
CY3R20	Rc1/8	NPT1/8	G1/8
CY3R25	Rc1/8	NPT1/8	G1/8
CY3R32	Rc1/8	NPT1/8	G1/8
CY3R40	Rc1/4	NPT1/4	G1/4
CY3R50	Rc1/4	NPT1/4	G1/4
CY3R63	Rc1/4	NPT1/4	G1/4

注2) *印はCY1Rシリーズと異なる寸法を示す。