


リングシールタイプアダプター


- Material : Plated steel
- 材質 : SS(三価クロメートメッキ)

SWO-T-G1G1W




呼び径	ねじT	Lmm	Amm	Bmm	Cmm	Dmm	Emm	φdmm	Fmm	HEX
6	G 1/4	45	13	9.5	32.3	21	7.5	5.5	17	19
9	G 3/8	52	15	11.0	36.9	24	8.8	8.0	19	22
12	G 1/2	62	17	14.0	43.0	27	10.0	11.0	22	27
19	G 3/4	72	20	16.0	49.0	30	11.0	16.0	30	32

SWO-T-G1WG1



呼び径	ねじT	Lmm	Amm	Bmm	Cmm	Dmm	Emm	φdmm	Fmm	HEX
6	G 1/4	55	22.5	13	13	9.5	7.5	5.5	17	19
9	G 3/8	63	26.0	15	15	11.0	8.8	8.0	19	22
12	G 1/2	74	31.0	17	17	14.0	10.0	11.0	22	27
19	G 3/4	86	36.0	20	20	16.0	11.0	16.0	30	32

ORFSS



呼び径	ねじT ₁ (UNS-UN)	ねじT ₂ (UNS-UN)	Lmm	Amm	Bmm	Cmm	dφmm	HEXmm 1 2	Oリング-1	Oリング-2
9/16 × 7/16	9/16-18	7/16-20	28.7	11.0	7.9	9.8	4.4	17.0 15.9	AS568-011	AS568-904
1 1/16 × 9/16	1 1/16-16	9/16-18	31.9	12.0	8.7	11.2	6.7	19.0 19.1	AS568-012	AS568-906
1 3/16 × 3/4	1 3/16-16	3/4-16	36.6	14.0	9.8	12.8	9.6	22.0 22.2	AS568-014	AS568-908
1 × 7/8	1-14	7/8-14	43.1	16.0	11.6	15.5	12.3	27.0 —	AS568-016	AS568-910
1 9/16 × 1 1/16	1 9/16-12	1 1/16-12	48.6	18.5	13.1	17.0	15.5	32.0 31.8	AS568-018	AS568-912
2 3/16 × 2 1/16	1 7/8-12	1 5/8-12	50.3	18.5	14.3	17.65	20.6	38.0 38.1	AS568-021	AS568-916
2 7/16 × 1 3/8	1 11/16-12	1 5/8-12	52.3	18.5	16.3	17.5	26.0	46.0 44.5	AS568-025	AS568-920
2 × 1 5/8	2-12	1 7/8-12	54.1	18.5	18.1	17.5	32.0	54.0 —	AS568-029	AS568-924

(注意) 予告なしに、品質・性能・改善のため寸法を変更する事があります。