


ストレートタイプアダプター

- Material : Plated steel.
- 材質 : SS(三価クロメートメッキ)

SR-13MR (メートルねじ)

SUSは受注生産




接続口金具 : SR-04(Mねじ)

呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	Cmm	dφmm	Lmm	HEXmm
14×6	M14-P1.5	R ¼	13	8	16.5	5.5	37.5	19
18×9	M18-P1.5	R ⅜	15	8	18.0	7.0	41.0	22
22×9	M22-P1.5	R ⅜	15	9	21.0	M10×R7	45.0	27
22×12	M22-P1.5	R ½	18	10	21.0	10.0	49.0	27
24×12	M24-P1.5	R ½	18	10	23.0	10.0	51.0	32
24×19	M24-P1.5	R ¾	20	12	23.0	13.0	55.0	32
30×19	M30-P1.5	R ¾	20	12	28.0	16.0	60.0	36
33×25	M33-P1.5	R 1	22	12	30.0	22.0	64.0	41

SR-13UR (ユニファイねじ)

*印及びSUSは受注生産




接続口金具 : SR-04(UNFねじ)

呼び径	ねじT ₁ UNF-UN	ねじT ₂ R	Amm	Bmm	Cmm	dφmm	Lmm	HEXmm
⅜×6	⅜-20	¼	13	7	14.0	4.4	34.0	17
½×6	½-20	¼	13	8	14.0	5.5	35.0	19
⅝×9	⅝-18	⅝	15	8	14.1	7.0	37.1	19
¾×12	¾-16	½	18	9	16.7	10.0	43.7	24
⅞×12	⅞-14	½	18	10	19.3	10.0	47.3	27
1⅞×19	1⅞-12	¾	20	12	21.9	16.0	53.9	36
1⅝×25	1⅝-12	1	22	12	24.0	22.0	57.1	41
* 1⅝×32	1⅝-12	1¼	25	14	24.3	28.0	63.3	50
* 1⅞×38	1⅞-12	1½	25	14	27.5	34.0	66.5	60

SR-13L

SUSは受注生産



接続口金具 : SR-04

呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	Cmm	dφmm	Lmm	HEXmm
6	G ¼	R ¼	50	8	16.0	5.5	74.0	19
9	G ⅜	R ⅜	53	10	17.5	8.0	80.5	22
12	G ½	R ½	65	10	20.0	11.0	95.0	27
19	G ¾	R ¾	78	14	21.5	16.0	113.5	36
25	G 1	R 1	83	14	22.5	22.0	119.5	41