


エルボータイプアダプター

- Material : Plated steel
- 材質 : SS(三価クロメートメッキ)

UL-90 (16)


*印及びSUSは受注生産



呼び径	ねじT ₁	ねじT ₂	Amm	Bmm	Cmm	dφmm	E ₁ mm	HEXmm
6	G ¼	R ¼	27.0	25.0	17	5.5	17	19
9	G ⅜	R ⅜	32.0	30.0	20	7.0	19	22
12	G ½	R ½	36.0	36.0	24	10.0	24	27
19	G ¾	R ¾	43.0	43.0	28	16.0	30	36
25	G 1	R 1	49.0	50.0	32	22.0	36	41
* 32	G1¼	R1¼	60.5	57.5	35	28.0	45	50
* 38	G1½	R1½	65.0	63.0	38	34.0	50	60
* 50	G 2	R 2	75.5	73.5	42	45.0	63	70

UL-90 (1609)

*印及びSUSは受注生産




接続口金具 : SR-05

呼び径	ねじT	Amm	Bmm	Cmm	dφmm	E ₁ mm	HEXmm
6	G ¼	27.0	21.0	13	5.5	17	19
9	G ⅜	32.0	25.0	15	7.0	19	22
12	G ½	36.0	30.0	18	10.0	24	27
19	G ¾	43.0	35.0	20	16.0	30	36
25	G 1	49.0	40.0	22	22.0	36	41
* 32	G1¼	60.5	46.5	25	28.0	45	50
* 38	G1½	65.0	49.0	25	34.0	50	60
* 50	G 2	75.5	59.5	30	45.0	63	70

UL-90 (1613)

*印及びSUSは受注生産



接続口金具 : SR-04

呼び径	ねじT	Amm	Bmm	Cmm	dφmm	E ₁ mm	HEXmm
6	G ¼	27.0	24.0	16.0	5.5	17	19
9	G ⅜	32.0	27.5	17.5	7.0	19	22
12	G ½	36.0	32.0	20.0	10.0	24	27
19	G ¾	43.0	36.5	21.5	16.0	30	36
25	G 1	49.0	40.5	22.5	22.0	36	41
* 32	G1¼	60.5	49.5	27.0	28.0	45	50
* 38	G1½	65.0	52.0	27.0	34.0	50	60
* 50	G 2	75.5	61.5	30.0	45.0	63	70