


リングシールタイプアダプター

- Material : Plated steel
- 材質 : SS(三価クロメートメッキ)

SSO-07 (同径)




接続口金具 : SR-01

\*印及びSUSは受注生産

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	dφmm	Lmm	HEXmm
6	Rc ¼	G ¼	11	17	5.5	28	19
9	Rc ⅜	G ⅜	11	19	8.0	30	22
12	Rc ½	G ½	15	22	11.0	37	27
19	Rc ¾	G ¾	16	25	16.0	41	36
25	Rc 1	G 1	18	27	22.0	45	41
* 32	Rc1¼	G1¼	20	30	28.0	50	50
* 38	Rc1½	G1½	22	30	34.0	52	60
* 50	Rc 2	G 2	25	36	45.0	61	70

SSO-07 (異径)




接続口金具 : SR-01

SUSは受注生産

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	dφmm	Lmm	HEXmm
6×9	Rc¼	G⅜	11	17	8.0	28	22
9×12	Rc⅜	G½	15	19	11.0	34	27
12×19	Rc½	G¾	16	22	16.0	38	36
19×25	Rc¾	G1	18	25	22.0	43	41
9×6	Rc⅜	G¼	11	19	5.5	30	22
12×9	Rc½	G⅜	11	22	8.0	33	27
19×12	Rc¾	G½	15	25	11.0	40	36
25×19	Rc 1	G¾	16	27	16.0	43	41

SSO-09 (同径)




接続口金具 : SR-05

\*印及びSUSは受注生産

呼び径	ねじT	Amm	Bmm	Cmm	dφmm	Lmm	HEXmm
6	G ¼	11	8	13	5.5	32	19
9	G ⅜	11	8	15	8.0	34	22
12	G ½	15	10	18	11.0	43	27
19	G ¾	16	12	20	16.0	48	36
25	G 1	18	12	22	22.0	52	41
* 32	G1¼	20	14	24	28.0	58	50
* 38	G1½	22	14	24	34.0	60	60
* 50	G 2	25	17	28	45.0	70	70

SSO-09 (異径)



接続口金具 : SR-05

SUSは受注生産

呼び径	ねじT <sub>1</sub>	ねじT <sub>2</sub>	Amm	Bmm	Cmm	d <sub>1</sub> φmm	d <sub>2</sub> φmm	Lmm	HEXmm
6×9	G¼	G⅜	11	8	13	5.5	7.0	32	22
9×12	G⅜	G½	15	10	15	7.0	10.0	40	27
12×19	G½	G¾	16	10	18	10.0	16.0	44	36
19×25	G¾	G1	18	12	20	16.0	22.0	50	41
9×6	G⅜	G¼	11	8	15	7.0	5.5	34	19
12×9	G½	G⅜	11	10	18	10.0	7.0	39	22
19×12	G¾	G½	15	12	20	16.0	10.0	47	27
25×19	G 1	G¾	16	12	22	22.0	16.0	50	36

(注意) 予告なしに、改善(品質・性能・価格等)の為寸法等を変更する事がありますのでご了承ください。