


RXE	3 ■■■■ 型式番号
RXH	

複式内管固定ねじ取付け



(mm)

サイズ	型式番号	A	C	E	F	G	D	L	L1	L3	L4	L5	d	W	内管				
															サイズ	i	B	S	T
15A	3015	R1/2	Rc1/2	Rc3/8	24	25	53	153	141	91	29	18	12.5	22	6A	10.5	G1/8	22	133
	3115	G1/2	Rc1/2	Rc3/8	24	25	53	155	143	93	31	18	12.5	27	6A	10.5	G1/8	22	135
	3215	M22×1.5	Rc1/2	Rc3/8	24	25	53	155	143	93	31	18	12.5	27	6A	10.5	G1/8	22	135
	3615	NPT1/2	NPT1/2	NPT3/8	24	25	53	153	141	91	29	18	12.5	22	6A	10.5	G1/8	22	133
	3715	3/4-16UNF	NPT1/2	NPT3/8	24	25	53	155	143	93	31	18	12.5	27	6A	10.5	G1/8	22	135
20A	3020	R3/4	Rc1/2	Rc3/8	30	28	65	164	152	98	32	19	18	32	8A	13.8	G1/4	23	144
	3120	G3/4	Rc1/2	Rc3/8	30	28	65	164	152	98	32	17	18	32	8A	13.8	G1/4	23	144
	3220	M26×1.5	Rc1/2	Rc3/8	30	28	65	164	152	98	32	17	18	32	8A	13.8	G1/4	23	144
	3620	NPT3/4	NPT1/2	NPT3/8	30	28	65	164	152	98	32	19	18	32	8A	13.8	G1/4	23	144
	3720	1-14UNS	NPT1/2	NPT3/8	30	28	65	164	152	98	32	17	18	32	8A	13.8	G1/4	23	144
25A	3025	R1	Rc3/4	Rc1/2	33	33	72	187	174	110	37	22	22	36	10A	17.3	G3/8	26	163
	3125	G1	Rc3/4	Rc1/2	33	33	72	183	170	106	33	18	22	36	10A	17.3	G3/8	26	159
	3225	M35×1.5	Rc3/4	Rc1/2	33	33	72	184	171	107	34	16	22	41	10A	17.3	G3/8	26	160
	3625	NPT1	NPT3/4	NPT1/2	33	33	72	187	174	110	37	22	22	36	10A	17.3	G3/8	26	163
	3725	1½-12UNF	NPT3/4	NPT1/2	33	33	72	191	178	114	41	23	22	41	10A	17.3	G3/8	26	167
32A	3032	R1¼	Rc1	Rc3/4	36	40	83	219	202	132	45	25	30	41	15A	21.7	G1/2	30	189
	3132	G1¼	Rc1	Rc3/4	36	40	83	220	203	133	46	25	30	41	15A	21.7	G1/2	30	190
	3232	M42×1.5	Rc1	Rc3/4	36	40	83	220	203	133	46	25	30	41	15A	21.7	G1/2	30	190
	3632	NPT1¼	NPT1	NPT3/4	36	40	83	219	202	132	45	25	30	41	15A	21.7	G1/2	30	189
	3732	1¾-12UN	NPT1	NPT3/4	36	40	83	220	203	133	46	25	30	41	15A	21.7	G1/2	30	190
40A	3040	R1½	Rc1	Rc3/4	39	43	89	226	209	137	47	25	35	46	20A	27.2	G3/4	32	196
	3140	G1½	Rc1	Rc3/4	39	43	89	227	210	138	48	25	35	46	20A	27.2	G3/4	32	197
	3240	M50×1.5	Rc1	Rc3/4	39	43	89	227	210	138	48	25	35	46	20A	27.2	G3/4	32	197
	3640	NPT1½	NPT1	NPT3/4	39	43	89	226	209	137	47	25	35	46	20A	27.2	G3/4	32	196
	3740	2-12UN	NPT1	NPT3/4	39	43	89	227	210	138	48	25	35	46	20A	27.2	G3/4	32	197
50A	3050	R2	Rc1½	Rc1	50	51	115	268	247	164	56	30	48	60	25A	34.0	G1	34	233
	3650	NPT2	NPT1½	NPT1	50	51	115	268	247	164	56	30	48	60	25A	34.0	G1	34	233
65A	3065	R2½	Rc2	Rc1½	68	62	123	345	315	206	75	40	58	65	32A	42.7	G1¼	45	293
	3665	NPT2½	NPT2	NPT1½	68	67	123	375	327	206	75	40	58	65	32A	42.7	G1¼	45	293
80A	3080	R3	Rc2	Rc1½	72	62	138	352	322	212	75	40	68	75	40A	48.6	G1½	45	300
	3680	NPT3	NPT2	NPT1½	72	67	138	382	334	212	75	40	68	75	40A	48.6	G1½	45	300

注記)Bは右ねじです。