

基準包装単位表

STANDARD PACKING UNIT TABLE

| 呼び直径 (mm) Nominal ball diameter | 呼 び Size | 1 個正味重量 (g) Weight/pcs | 転がり軸受用鋼球 Steel balls for rolling bearings (SUJ2,SUS440C) | | 炭素鋼球 Carbon steel balls | | ステンレス鋼球 Stainless steel balls (SUS304,SUS316) | |
|--|-------------|------------------------------|--|---|--|---|---|---|
| | | | 紙 函 入数(個) Packing quantity per box | ダンボール函 入数(個) Packing quantity per carton case | 紙 函 入数(個) Packing quantity per box | ダンボール函 入数(個) Packing quantity per carton case | 紙 函 入数(個) Packing quantity per box | ダンボール函 入数(個) Packing quantity per carton case |
| 0.4000 | 0.4 | 0.0002604 | 50,000 | | | | | |
| 0.5000 | 0.5 | 0.0005085 | 50,000 | | | | | |
| 0.6000 | 0.6 | 0.0008788 | 50,000 | | | | | |
| 0.7000 | 0.7 | 0.001385 | 50,000 | | | | | |
| 0.7938 | 1/32 | 0.002035 | 50,000 | | | | | |
| 0.8000 | 0.8 | 0.002083 | 20,000 | | | | | |
| 1.0000 | 1.0 | 0.004063 | 20,000 | | | | | |
| 1.1906 | 3/64 | 0.006866 | 30,000 | | | | | |
| 1.2000 | 1.2 | 0.007030 | 20,000 | | | | | |
| 1.5000 | 1.5 | 0.01373 | 20,000 | | | | | |
| 1.5875 | 1/16 | 0.01628 | 20,000 | | | | | |
| 1.9844 | 5/64 | 0.03179 | 20,000 | | | | | |
| 2.0000 | 2.0 | 0.03255 | 20,000 | | 10,000 | | 8,000 | |
| 2.3813 | 3/32 | 0.05493 | 30,000 | 300,000 | 20,000 | 320,000 | 30,000 | |
| 2.5000 | 2.5 | 0.06357 | 30,000 | 300,000 | 30,000 | 300,000 | | |
| 2.7781 | 7/64 | 0.08723 | 20,000 | 200,000 | 20,000 | 200,000 | 20,000 | 200,000 |
| 3.0000 | 3.0 | 0.1098 | 40,000 | 200,000 | 10,000 | 160,000 | 40,000 | 200,000 |
| 3.1750 | 1/8 | 0.1302 | 30,000 | 150,000 | 40,000 | 200,000 | 30,000 | 150,000 |
| 3.5000 | 3.5 | 0.1744 | 24,000 | 120,000 | | | 24,000 | 120,000 |
| 3.5719 | 9/64 | 0.1854 | 24,000 | 120,000 | | | | |
| 3.9688 | 5/32 | 0.2543 | 16,000 | 80,000 | 20,000 | 100,000 | 16,000 | 80,000 |
| 4.0000 | 4.0 | 0.2604 | 16,000 | 80,000 | 20,000 | 100,000 | 16,000 | 80,000 |
| 4.3656 | 11/64 | 0.3385 | 10,000 | 50,000 | | | | |
| 4.5000 | 4.5 | 0.3707 | 10,000 | 50,000 | | | 10,000 | 50,000 |
| 4.7625 | 3/16 | 0.4395 | 10,000 | 50,000 | 12,000 | 60,000 | 10,000 | 50,000 |
| 5.0000 | 5.0 | 0.5085 | 8,000 | 40,000 | 10,000 | 50,000 | 8,000 | 40,000 |
| 5.5563 | 7/32 | 0.6979 | 6,000 | 30,000 | 7,000 | 35,000 | 6,000 | 30,000 |
| 5.9531 | 15/64 | 0.8583 | 5,000 | 25,000 | | | | |
| 6.0000 | 6.0 | 0.8788 | 5,000 | 25,000 | 6,000 | 30,000 | 5,000 | 25,000 |
| 6.3500 | 1/4 | 1.042 | 4,000 | 20,000 | 5,000 | 25,000 | 4,000 | 20,000 |
| 6.7469 | 17/64 | 1.249 | 3,500 | 17,500 | | | | |
| 7.1438 | 9/32 | 1.483 | 3,000 | 15,000 | 3,500 | 17,500 | 3,000 | 15,000 |
| 7.9375 | 5/16 | 2.035 | 2,000 | 10,000 | 2,500 | 12,500 | 2,000 | 10,000 |
| 8.0000 | 8.0 | 2.083 | 2,000 | 10,000 | 2,500 | 12,500 | | |
| 8.7313 | 11/32 | 2.708 | 1,600 | 8,000 | 2,000 | 10,000 | | |
| 9.5250 | 3/8 | 3.516 | 1,200 | 6,000 | 1,500 | 7,500 | 588 | 2,940 |
| 10.0000 | 10.0 | 4.068 | 1,000 | 5,000 | 1,100 | 5,500 | | |
| 10.3188 | 13/32 | 4.470 | 1,000 | 5,000 | 1,100 | 5,500 | | |
| 11.1125 | 7/16 | 5.583 | 800 | 4,000 | 900 | 4,500 | 300 | 1,500 |
| 11.9063 | 15/32 | 6.867 | 600 | 3,000 | | | | |
| 12.7000 | 1/2 | 8.334 | 500 | 2,500 | 600 | 3,000 | 240 | 1,200 |
| 13.0000 | 13.0 | 8.938 | 500 | 2,500 | | | | |
| 13.4938 | 17/32 | 9.996 | 400 | 2,000 | | | | |
| 14.0000 | 14.0 | 11.16 | 380 | 1,900 | | | | |
| 14.2875 | 9/16 | 11.87 | 350 | 1,750 | 400 | 2,000 | 140 | 700 |