


New

SOLIDMEISTER

TEB**A2H

2枚刃、ねじれ角30°、ボールエンドミル、ロングネックタイプ、高硬度鋼加工用



形番	AH3005	DC	DCONMS	NOF	DN	RE	APMX	LH	BHTA	LF	シャンク
TEB003A2-006/75/15C4H-45	●	0.3	4	2	-	0.15	0.6	-	15°	45	円筒
TEB003A2-003/01C4H-45	●	0.3	4	2	0.27	0.15	0.3	1	15°	45	円筒
TEB003A2-003/02C4H-45	●	0.3	4	2	0.27	0.15	0.3	2	15°	45	円筒
TEB004A2-008/75/15C4H-45	●	0.4	4	2	-	0.2	0.8	-	15°	45	円筒
TEB004A2-004/01C4H-45	●	0.4	4	2	0.36	0.2	0.4	1	15°	45	円筒
TEB004A2-004/015C4H-45	●	0.4	4	2	0.36	0.2	0.4	1.5	15°	45	円筒
TEB004A2-004/02C4H-45	●	0.4	4	2	0.36	0.2	0.4	2	15°	45	円筒
TEB004A2-004/025C4H-45	●	0.4	4	2	0.36	0.2	0.4	2.5	15°	45	円筒
TEB004A2-004/03C4H-45	●	0.4	4	2	0.36	0.2	0.4	3	15°	45	円筒
TEB004A2-004/04C4H-45	●	0.4	4	2	0.36	0.2	0.4	4	15°	45	円筒
TEB005A2-010/75/15C4H-45	★	0.5	4	2	-	0.25	1	-	15°	45	円筒
TEB005A2-005/01C4H-45	★	0.5	4	2	0.45	0.25	0.5	1	15°	45	円筒
TEB005A2-005/015C4H-45	●	0.5	4	2	0.45	0.25	0.5	1.5	15°	45	円筒
TEB005A2-005/02C4H-45	●	0.5	4	2	0.45	0.25	0.5	2	15°	45	円筒
TEB005A2-005/025C4H-45	●	0.5	4	2	0.45	0.25	0.5	2.5	15°	45	円筒
TEB005A2-005/03C4H-45	●	0.5	4	2	0.45	0.25	0.5	3	15°	45	円筒
TEB005A2-005/04C4H-45	●	0.5	4	2	0.45	0.25	0.5	4	15°	45	円筒
TEB006A2-012/75/15C4H-45	●	0.6	4	2	-	0.3	1.2	-	15°	45	円筒
TEB006A2-006/02C4H-45	●	0.6	4	2	0.55	0.3	0.6	2	15°	45	円筒
TEB006A2-006/02C6H-45	●	0.6	6	2	0.55	0.3	0.6	2	15°	45	円筒
TEB006A2-006/03C4H-45	☆	0.6	4	2	0.55	0.3	0.6	3	15°	45	円筒
TEB006A2-006/04C4H-45	●	0.6	4	2	0.55	0.3	0.6	4	15°	45	円筒
TEB006A2-006/04C6H-45	●	0.6	6	2	0.55	0.3	0.6	4	15°	45	円筒
TEB006A2-006/05C4H-45	●	0.6	4	2	0.55	0.3	0.6	5	15°	45	円筒
TEB006A2-006/06C4H-45	●	0.6	4	2	0.55	0.3	0.6	6	15°	45	円筒
TEB006A2-006/06C6H-45	●	0.6	6	2	0.55	0.3	0.6	6	15°	45	円筒
TEB008A2-016/76/15C4H-45	●	0.8	4	2	-	0.4	1.6	-	15°	45	円筒
TEB008A2-008/02C4H-45	●	0.8	4	2	0.75	0.4	0.8	2	15°	45	円筒
TEB008A2-008/02C6H-45	●	0.8	6	2	0.75	0.4	0.8	2	15°	45	円筒
TEB008A2-008/03C4H-45	●	0.8	4	2	0.75	0.4	0.8	3	15°	45	円筒
TEB008A2-008/04C4H-45	●	0.8	4	2	0.75	0.4	0.8	4	15°	45	円筒
TEB008A2-008/04C6H-45	●	0.8	6	2	0.75	0.4	0.8	4	15°	45	円筒
TEB008A2-008/06C4H-45	●	0.8	4	2	0.75	0.4	0.8	6	15°	45	円筒
TEB008A2-008/06C6H-45	●	0.8	6	2	0.75	0.4	0.8	6	15°	45	円筒
TEB010A2-025/118/15C6H-50	●	1	6	2	-	0.5	2.5	-	15°	50	円筒
TEB010A2-015/025C6H-38	●	1	6	2	0.95	0.5	1.5	2.5	15°	38	円筒
TEB010A2-010/03C4H-50	●	1	4	2	0.97	0.5	1	3	15°	50	円筒
TEB010A2-010/03C6H-50	●	1	6	2	0.95	0.5	1	3	15°	50	円筒
TEB010A2-010/04C4H-50	●	1	4	2	0.97	0.5	1	4	15°	50	円筒
TEB010A2-010/04C6H-50	●	1	6	2	0.95	0.5	1	4	15°	50	円筒
TEB010A2-010/05C4H-50	●	1	4	2	0.97	0.5	1	5	15°	50	円筒
TEB010A2-010/06C4H-50	●	1	4	2	0.97	0.5	1	6	15°	50	円筒
TEB010A2-010/06C6H-50	●	1	6	2	0.95	0.5	1	6	15°	50	円筒
TEB010A2-010/08C4H-50	●	1	4	2	0.95	0.5	1	8	15°	50	円筒
TEB010A2-010/08C6H-50	●	1	6	2	0.95	0.5	1	8	15°	50	円筒
TEB010A2-010/10C4H-50	●	1	4	2	0.95	0.5	1	10	15°	50	円筒
TEB010A2-010/10C6H-50	●	1	6	2	0.95	0.5	1	10	15°	50	円筒
TEB010A2-010/12C4H-50	●	1	4	2	0.93	0.5	1	12	15°	50	円筒
TEB015A2-040/124/15C6H-50	●	1.5	6	2	-	0.75	4	-	15°	50	円筒
TEB015A2-015/04C4H-50	●	1.5	4	2	1.45	0.75	1.5	4	15°	50	円筒

●: 新製品

★: 2025年2月発売予定アイテム

☆: 2025年3月発売予定アイテム

参照ページ: 標準切削条件 → P63 - 65, テクニカルガイド → P66