

LSLE-BS

BS柄ロング2枚刃エンドミル

2-Flutes Long End Mill with BS Shank

外径 φ D	刃長 L c	柄 NO.	全長 L	柄長 L 1	刃数
31	120	BS9	253	120	2
32	80	BS9	213	120	2
32	100	BS9	233	120	2
32	120	BS9	253	120	2
32	150	BS9	283	120	2
32	200	BS9	333	120	2
33	120	BS9	253	120	2
34	100	BS9	233	120	2
34	120	BS9	253	120	2
35	80	BS9	213	120	2
35	100	BS9	233	120	2
35	120	BS9	253	120	2
35	150	BS9	283	120	2
35	200	BS9	333	120	2
35	250	BS9	383	120	2
36	80	BS9	213	120	2
36	100	BS9	233	120	2
36	120	BS9	253	120	2
36	150	BS9	283	120	2
37	120	BS9	253	120	2
38	80	BS9	213	120	2
38	100	BS9	233	120	2
38	120	BS9	253	120	2
38	150	BS9	283	120	2
38	200	BS9	333	120	2
38	250	BS9	383	120	2
39	100	BS9	235	120	2
39	120	BS9	255	120	2
40	80	BS9	215	120	2
40	100	BS9	235	120	2
40	120	BS9	255	120	2
40	150	BS9	285	120	2
40	200	BS9	335	120	2
40	250	BS9	385	120	2
41	100	BS9	235	120	2
41	120	BS9	255	120	2
42	100	BS9	235	120	2
42	120	BS9	255	120	2
42	150	BS9	285	120	2
43	100	BS9	235	120	2
43	120	BS9	255	120	2
44	100	BS9	235	120	2
44	120	BS9	255	120	2
45	80	BS9	215	120	2
45	100	BS9	235	120	2
45	120	BS9	255	120	2
45	150	BS9	285	120	2
45	200	BS9	335	120	2
45	250	BS9	385	120	2
46	100	BS9	235	120	2
46	120	BS9	255	120	2
46	150	BS9	285	120	2
47	120	BS9	255	120	2
48	100	BS9	235	120	2
48	120	BS9	255	120	2
48	150	BS9	285	120	2
49	100	BS9	235	120	2
49	120	BS9	255	120	2
50	100	BS9	235	120	2