


C-KC

超硬ソリッドキーシードカッター

Carbide Solid Woodruff Key-Seat Cutter



在庫がなくなった寸法より先ムクからソリッドに変更しております。



外径許容差(φD) 10以上 30以下 0～+0.05
30を超え 50以下 0～+0.07
刃幅許容差(Lc) 外径 10以上 30以下 -0.012～0
外径 30を超え 50以下 -0.018～0

Z20

外径 φD	刃幅 Lc	柄径 φd	柄長 (L1)	首径 φd1	首長(フラット) L2	全長 L	刃数
10	0.4	8	74.2	4.5	7	85	8
10	0.5	8	74.1	4.5	7	85	8
10	0.6	8	74	4.5	7	85	8
10	0.7	8	73.9	4.5	7	85	8
10	0.8	8	73.8	4.5	7	85	8
10	0.9	8	73.7	4.5	7	85	8
10	1	8	73.6	4.5	7	85	8
10	1.1	8	73.5	4.5	7	85	8
10	1.2	8	73.4	4.5	7	85	8
10	1.3	8	73.3	4.5	7	85	8
10	1.4	8	73.2	4.5	7	85	8
10	1.5	8	73.1	4.5	7	85	8
10	1.6	8	73	4.5	7	85	8
10	1.7	8	72.9	4.5	7	85	8
10	1.8	8	72.8	4.5	7	85	8
10	1.9	8	72.7	4.5	7	85	8
10	2	8	72.6	4.5	7	85	8
10	2.1	8	72.5	4.5	7	85	8
10	2.2	8	72.4	4.5	7	85	8
10	2.3	8	72.3	4.5	7	85	8
10	2.4	8	72.2	4.5	7	85	8
10	2.5	8	72.1	4.5	7	85	8
10	2.6	8	72	4.5	7	85	8
10	2.7	8	71.9	4.5	7	85	8
10	2.8	8	71.8	4.5	7	85	8
10	2.9	8	71.7	4.5	7	85	8
10	3	8	71.6	4.5	7	85	8
10	3.5	8	71.1	4.5	7	85	8
10	4	8	70.6	4.5	7	85	8
10	5	8	69.6	4.5	7	85	8
12	0.4	10	73.5	5	7	85	8
12	0.5	10	73.4	5	7	85	8
12	0.6	10	73.3	5	7	85	8
12	0.7	10	73.2	5	7	85	8
12	0.8	10	73.1	5	7	85	8
12	0.9	10	73	5	7	85	8
12	1	10	72.9	5	7	85	8
12	1.1	10	72.8	5	7	85	8
12	1.2	10	72.7	5	7	85	8
12	1.3	10	72.6	5	7	85	8
12	1.4	10	72.5	5	7	85	8

被削材種 型番	鋳物	炭素鋼	合金鋼	工具鋼	調質鋼	ステンレス鋼	アルミ合金	銅合金	チタン合金	耐熱合金
	FC,FCD	S45C	SCM	SKD	NAK,HPM	SUS	Al	Cu	Ti6Al4V	インコネル
硬度	~200HB	~200HB	~250HB	~35HRC	~45HRC					
C-KC	○	○	○	○	△	○	○	○		

切削条件 P.293