

# 60900 FLEXIBLE STEM MAGNETIC STAND SERIES / 蛇形万向磁力表座

## FEATURES

- The flexible stem magnetic base is an ideal testing tool at random angle and internal hole
- Flexible stem easy reach the place which is hard for rigid stem to reach
- Flexible stem with locking lever and inching adjuster, adjustable to any position



## 60905 FLEXIBLE STEM MAGNETIC STAND

- Magnetic base with On/Off switch
- With fine adjustment
- Dovetail groove for test indicator
- Clamp hole 8mm ( optional : hole 3/8" )
- Overall stem length 360 mm
- Tapped hole : M8 x 1.25 mm
- Weight : 1.3kg



Code	Model	Magnetic force	Base(L x W x H)
60905-011	CV-6CA	60 kg	58 x 50 x 55
60905-021	CV-8CA	80 kg	60 x 50 x 55
60905-111	CV-6CA- I	60 kg	58 x 50 x 55
60905-121	CV-8CA- I	80 kg	60 x 50 x 55

## 60910 FLEXIBLE STEM MAGNETIC STAND

- Magnetic base with On/Off switch
- Clamp hole accept all test indicators and normal indicators
- Overall stem length 320 mm
- Tapped hole : M8 x 1.25 mm
- Weight : 1.3 kg



Code	Model	Magnetic force	Base(L x W x H)
60910-011	CV-6CB	60 kg	58 x 50 x 55
60910-021	CV-8CB	80 kg	60 x 50 x 55
60910-111	CV-6CB- I	60 kg	58 x 50 x 55
60910-121	CV-8CB- I	80 kg	60 x 50 x 55